

Tubes verre acrylique "extrudés"

(Longueur standard 2 m.)

\emptyset EXT. MM	\emptyset INT. MM	EPAISSEUR PAROI MM	TOLERANCE \emptyset EXT \pm MM	TOLERANCE PAROI \pm		\emptyset EXT MM	\emptyset INT. MM	EPAISSEUR PAROI MM	TOLERANCE \emptyset EXT \pm MM	TOLERANCE PAROI \pm	
<u>5</u>	3	1	0.3	0.2		<u>60</u>	56	2	0.8	0.25	
							54	3		0.35	
<u>6</u>	3.5	1.25	0.3			<u>50</u>	5		0.4		
<u>6.5</u>	4	1.25	0.3	0.2		<u>70</u>	64	3	0.8	0.35	
<u>7</u>	5	1	0.3	0.2			62	4		0.4	
<u>8</u>	4	2	0.3	0.3			60	5		0.4	
<u>10</u>	7	1.5	0.3	0.2		<u>80</u>	74	3	0.9	0.35	
	6	2		0.25			72	4		0.4	
	4	3		0.3			70	5		0.45	
<u>12</u>	10	1	0.3	0.2		<u>90</u>	84	3	0.9	0.35	
	8	2		0.25			82	4		0.4	
	6	3		0.3			80	5		0.45	
<u>13</u>	10	1.5	0.3	0.25		<u>100</u>	94	3	1.2	0.35	
	9	2		0.25			92	4		0.4	
							90	5		0.45	
<u>15</u>	13	1	0.3	0.2		<u>110</u>	104	3	1.2	0.35	
	11	2		0.25			100	5		0.45	
	10	2.5		0.3		<u>120</u>	114	3	1.2	0.35	
<u>16</u>	12	2	0.3	0.25			110	5		0.45	
<u>20</u>	18	1	0.3	0.2		<u>133</u>	127	3	1.3	0.35	
	16	2		0.25			123	5		0.5	
	14	3		0.3		<u>150</u>	144	3	1.5	0.4	
<u>25</u>	21	2	0.3	0.25			142	4		0.45	
	19	3	0.3	0.3			140	5		0.5	
<u>30</u>	26	2	0.5	0.25		<u>180</u>	172	4	1.5	0.45	
	24	3		0.3		<u>200</u>	194	3	2.0	0.4	
	22	4		0.35			192	4		0.5	
	20	5		0.4			190	5		0.55	
<u>40</u>	36	2	0.5	0.25		BLANC (DIFFUSEUR)					
	34	3		0.3		<u>150</u>	144	3	1.5	0.4	
	32	4		0.35		<u>200</u>	194	3	2.0	0.4	
	30	5		0.4							
<u>50</u>	46	2	0.8	0.25							
	44	3		0.3							
	42	4		0.35							
	40	5		0.4							

